Transportable Resistance Standards

SR-102/SR-103/SR-104 p. 1 of 2

These Transportable Resistance Standards are designed for precision applications. Their accuracy, stability, and low temperature coefficient make them ideal for precise laboratory comparisons without critical environmental controls. For maximum accuracy, these standards offer users a temperaturecorrection chart and a built-in RTD temperature sensor to measure internal temperature.



Temperature coefficient comparison between a typical SR-102 unit and a typical 100 Ω resistance standard

SPECIFICATIONS •

Stability

First 2 years: ±1 ppm/year **Thereafter:** ±0.5 ppm/year

Temperature coefficient

 $\begin{array}{l} \mbox{Temperature coefficient } (\alpha): $<0.1 \ \mbox{ppm/}^{\circ}C \ \mbox{at } 23^{\circ}C $\\ \mbox{1/2 rate of TC change } (\beta): $<0.03 \ \mbox{ppm/}^{\circ}C \ \mbox{from } 18^{\circ}C \ \mbox{to } 28^{\circ}C $\\ α \ \mbox{and } \beta$ \ \mbox{are determined by the following expression: $$R_{s}=R_{23}[1+\alpha_{23}(t-23)+\beta(t-23)^{2}]$ $\\ $$where R_{s} = Standard Resistance at temperature t $$ $$tandard temperature t $$} $\\ \end{tabular}$

No ovens or external power required

Power coefficient

<1 ppm/W

Adjustment to nominal

±1 ppm

Measurement uncertainty <0.32 ppm

Max voltage

```
500 V peak to case
```

Power rating

1 W (Momentary 100 W overloads will not cause failure)

Thermal emf

Thermal emf at the terminals does not exceed $\pm 0.1 \ \mu V$ under normal conditions.

Insulation resistance

All terminals maintain a minimum $10^{\mbox{\tiny 12}}\,\Omega$ to ground

Features

- High accuracy
- High stability -- <0.2 ppm/year
- Low temperature coefficient -- <0.1 ppm/°C
- · Built-in temperature sensor and temperature-correction chart
- Oil-filled
- · Hermetically sealed
- · Increased-stability option (DC) is available to be used in an oil-bath



Transportable Resistance Standard

Internal temperature sensor

100 Ω , 1 k Ω , or 10 k Ω resistor with 1,000 ppm/°C temperature coefficient. Integral thermometer well is provided for calibration

Hermetic sealing

To eliminate the effects of humidity, the resistor is hermetically sealed in oil with metal-to-glass seals. The resistance changes <±0.1 ppm with normal atmospheric pressure and humidity changes.

Pressure effects

No pressure effects under normal atmospheric changes.

Connection terminals

Five-terminal construction, four-terminal resistor with ground intercept for the standard and temperature resistor.

Thermal emf

Thermal emf at the terminals does not exceed $\pm 0.1 \ \mu V$ under normal conditions.

Thermal lagging

Thermal lagging time constant is 1 hour minimum (1-1/e of total change in one hour).

Dielectric soakage effect

The resistance stabilizes to within 0.1 ppm of final value within 5 seconds with 1 V applied to the resistor.

Current reversal

With the reversal of the current through the resistor, the resistance value changes less than ± 0.1 ppm.

Shock effects

The resistance changes is <0.2 ppm when subjected to 2 drops three-foot drops to a concrete floor on each of the 3 mutually perpendicular faces (6 drops total).

IET LABS, INC. in the **GenRad** Tradition 534 Main Street, Westbury, NY 11590 TEL: (

www.ietlabs.com

TEL: (516) 334-5959 • (800) 899-8438 • FAX: (516) 334-5988

SR-102/SR-103/SR-104 p. 2 of 2

SAMPLE TEMPERATURE CORRECTION CHART



MECHANICAL INFORMATION

Dimensions

Regular 25.4 cm x 20.6 cm x 31.1 cm (10" x 8.1" x 12.25") Deleted case (DC) version 12.7 cm x 8.9 cm x 17.8 cm (5.0" x 3.5" x 7.0")

Weight

Regular 4.8 kg (10.5 lb) Deleted case (DC) version 1.8 kg (4.0 lb)

OPTIONAL EXTERNAL OIL BATH

This optional version can further enhance the short-term stability of the resistance standard. It comes without the insulated case, so that it may be used in an external oil bath that provides additional temperature stability. This version is called Deleted Case (DC).

When the standards are used in an oil bath, the resistance elements maintain a constant temperature, providing outstanding short-term stability, which is especially important when making Quantum-Hall-Effect measurements.

ORDERING INFORMATION

100 ohm Transportable Resistance Standard:SR-1021,000 ohm Transportable Resistance Standard:SR-10310,000 ohm Transportable Resistance Standard:SR-104

Optional:

For deleted case version add **-DC** at the end of the part number.

Each unit includes:

- Built-in temperature sensor
- Temperature correction chart
- Instruction manual
- ISO/IEC 17025 calibration certificate
- **IET LABS, INC.** in the **GenRad** Tradition 534 Main Street, Westbury, NY 11590 TEL: (

radition www.ietlabs.com TEL: (516) 334-5959 • (800) 899-8438 • FAX: (516) 334-5988