

6HI HEXODE Indirectly heated—for parallel operation

GENERAL

The 6H1 is a miniature based hexode intended for use as a frequency changer with a separate triode oscillator, and will operate up to a frequency of 20 Mc/s. It is also suitable for use as a gated amplifier, and may be used in equipment having AC or DC powered parallel connected heater chains.

RATING

Heater Voltage	(volts)	Vh	6.3
Heater Current	(amps)	lh.	0.2
Maximum Anode Voltage	(volts)	Va(b)max	550†
Maximum Operating Anode Voltage	(volts)	V _{a(max)}	300
Maximum Screen Voltage	(volts)	Vg2,4(b)max	400†
Maximum Operating Screen Voltage	(volts)	Vg2,4(max)	300
Maximum Anode Dissipation	(watts)	Pa(max)	1.0
Maximum Screen Dissipation	(watts)	Pg2+4(max)	0.7
Mutual Conductance	(mA/V)	gm (2.1*
* Measured at $V_a = 250 \text{ V}$; $I_a = 0$.	Vg2+g4 =	= 100 V ; Vg1 =	–1·8V.

All Maximum Values quoted are absolute.

INTER-ELECTRODE CAPACITANCES (pF)

Anode/Grid 1	ca-g1	0-06
Anode/Earth	c _{a-E}	9.25
Grid 1/Earth	cg1-E	4-3
Grid 3/All	cg3-ali	4.9

[&]quot;Earth" denotes all earth potential electrodes, shields and heater connected to the cathode.

These capacities are measured cold with a metal screening can fitted to the valve.

Indicates a change

✓
Issue 1, Page 1



6H I HEXODE Indirectly heated—for parallel operation

DIMENSIONS		
Maximum Overall Length	(mm)	54∙5 ←
Maximum Diameter	(mm)	19∙0
Maximum Seated Height	(mm)	47∙5 ←
Approximate Nett Weight	(ozs)	14
Approximate Packed Weight	(ozs)	1/2

MOUNTING POSITION-Unrestricted.

TYPICAL OPERATION—Frequency Changer

Anode Voltage	(volts)	V_a	250
Screen Voltage	(volts)	Vg_2+4	100
Grid 1 Bias Voltage	(volts)	Vg1	-2·2 ←
Anode Current (approx)	(mA)	la	2⋅3* ←
Screen Current (approx)	(mA)	lg2+4	2.7* ←
Conversion Conductance	$(\mu A/V)$	gc	560† ←
Valve Anode Resistance $(\delta v_a/\delta i_a)$	(MΩ)	ra	1.0 ←
Peak Heterodyne Voltage	(volts)	$V_{het(pk)}$	12 ←
Grid 3 Resistor	$(k\Omega)$	Rg3	47*

^{*} Grid 3 connected in parallel with the grid of the oscillator valve and biased by grid current through the Grid 3 resistor.

Measured with an anode circuit of low dynamic impedance.

Indicates a change

✓
Issue 1, Page 2



6HI HEXODE Indirectly heated—for parallel operation

+

BASE-B7G



Viewed from free end of pins

VALVE HOLDER—Ediswan Clix VH337/7, VH437/7 and VH17/7 series.

CONNECTIONS

Pin 1	Grid 1	81
Pin 2	Cathode	k
Pin 3	H e ater	h
Pin 4	Heater	h
Pin 5	Anode	a
Pin 6	Grid 3	g3
Pin 7	Grid 2 and Grid 4	g2+g4

Indicates a change

✓
Issue 1, Page 3

6HI HEXODE

Indirectly heated—for parallel operation

AVERAGE CHARACTERISTIC CURVES:

gc.la.lg2.lg3.lg0/Vhet(pk) Heterodyne injected into g3

 $\begin{array}{lll} V_a &= 250V & V_{g2} = 100V \\ V_{g1} = -2\cdot 2V & Z_L = 49k\Omega \end{array}$

 V_{g3} = Self Bias $R_{g3} = 47k\Omega$

Note: g3 is connected in parallel with the grid of an external

oscillator and is biased by grid current.

