700E



INSTRUMENT **CATHODE RAY TUBE**

BRIEF DATA

The 700E has a 2 in. x 1 in. rectangular face and incorporates electrostatic focus and deflection. Low current flow to both x and y deflector plates enables numbers of tubes to be operated from common time base supplies. This together with the small dimensions of the tube and its high brightness makes the 700E particularly useful when the tube is to be used in banks for the display of digital information.

HEATER

SCREEN													
Heater current	•	•	٠	٠	•	•	•	•	•	•	•	0.3	Α
Heater voltage .												6.3	V

Tube normally su	ıpp	lied	w t	ith	24	ph	osț	ohc	or a	s 7:	248	Ξ.
Fluorescence												
Phosphorescence						_						

E.I.A. phosphor code	•	٠	٠		•	•							P31
GEC phosphor code .			•				•	•					24
Pro Electron phosphor	CO	de	•	•	•							٠	GH
Other screens are availa													

RATINGS (Absolute)

Focus voltage .

	•	•	1.0		ΚV
First & third anode voltage			2.5	1.5	kV
*Negative grid voltage			200	0	V
X deflector plate to a1, a3 voltage (peak).			500	_	V
Y deflector plate to a1, a3 voltage (peak).			500		V
Heater-cathode voltage			180		V
X deflector plate to a1, a3 circuit resistance			0.25	_	Ω M
Y deflector plate to a1, a3 circuit resistance			1.0	_	$M\Omega$

Max

1.0

Grid-cathode circuit resistance 1.5 МΩ *The dc value of the modulator voltage must never become positive with respect to cathode.

Green

Green 1 – 5 ms

kV

CAPACITANCES

Cathode to all		4	рF
Grid to all		7	ρF
Deflector plates x1 to x2		2	pF
Deflector plates y1 to y2		3	ρF
Deflector plates x1 to all electrodes except x2		5	ρF
Deflector plates y1 to all electrodes except y2		6	pF
Deflector plates x2 to all electrodes except x1		5	рF
Deflector plates y2 to all electrodes except y1		6	pF

TYPICAL OPERATION (for character generation)

First & third anode voltage	. V _{a1.3}	2.0	kV
Second anode voltage	V _{a2}	60	V
Control grid voltage for spot cut-off	$-V_0$	60 - 100	V
Maximum x deflection factor	. D,	46.0	V/cm
Maximum y deflection factor	. D.,	107.2	V/cm
Line width (typical) at $I_k = 500 \mu\text{A}$.		1.5	mm

CHARACTERISTICS

	Min	Max	
Focus voltage	2 10	45	$V/kV_{a1,3}$
Control grid voltage for spot cut-off -V ₀	30	50	$V/kV_{a1.3}$
X deflection factor D	20.4	23.0	V/cm/kV _{a1.3}
Y deflection factor D	44.5	53.6	V/cm/kV _{a1,3} MΩ
*Heater-cathode resistance rh-	_{-k} 1.5		MΩ
Grid-cathode resistance rg-	k 10		МΩ

^{*}With heater ±125V to cathode.

Pattern Distortion

The edges of a test raster will lie between two concentric rectangles of 46.5 mm x 20.75 mm and 43.5 mm x 19.25 mm.

Deflection Linearity

The deflection factor for a deflection of less than 75% of the useful scan will not differ from that for a deflection of 25% by more than 2%.

Orientation

Looking at the screen with the base spigot to the left, a positive potential applied to x1 will deflect the spot to the left and a positive potential applied to y1 will deflect the spot downwards.

Focus Current

The maximum focus electrode (a2) current will be 20 μA with the tube blacked out and V_{a2} = 60 V.

Deflector Plate Current

The maximum deflector plate current will be 7 μ A with a 4.5 x 2.0 cm raster and I_k = 500 μ A.

Minimum Scanned Area

X axis															4.5	cm
Y axis															2.4	cm
Angle b	etv	vee	n d	lefl	ect	ion	ax	es:	9	o° :	± 1	۰.				

Spot Position

The undeflected spot will lie within a circle of 3.0 mm radius centred on the tube face.

MOUNTING

The tube should not be supported by the base alone, but should preferably be held in a suitable rubber mask at the screen and by a clamp round the magnetic shield near the base.

WEIGHT

The weight of the tube is 170 g (6 oz).

BASE CONNECTIONS

Base: B12A

	· ·		
Pin 1:	h	Pin 7:	Y2
2: 3:	g	8:	a _{1,3}
3:	k	9:	X2
4:	∂ 2	10:	Χį
5:	NC	11:	NC
6:	У1	12:	h

SOCKET

The socket should have sufficient freedom of movement to accommodate the tube overall length and base orientation tolerances.

MAGNETIC SHIELDING

accordance with information contained herein.

The shield should be of high permeability material, of a thickness determined by the magnetic field at the tube position. The shield should be earthed. A suitable shield is available from Magnetic Shields Ltd., Headcorn Road,

Staplehurst, Tonbridge, Kent.

Whilst M-OV has taken care to ensure the accuracy of the information contained herein

it accepts no responsibility for the consequences of any use thereof and also reserves the right to change the specification of goods without notice.

M-OV accepts no liability beyond that set out in its standard conditions of sale in respect of infringement of third party patents arising from the use of tubes or other devices in

700E

OUTLINE

