

**ELECTRICAL** 

## 24CP4-A CATHODE-RAY TUBE

21%- BY 16%-INCH PICTURE SIZE

24-INCH RECTANGULAR, GLASS FOCUS—MAGNETIC DEFLECTION—MAGNETIC 90-DEGREE DEFLECTION ANGLE

FACEPLATE—SPHERICAL, GRAY
ION-TRAP GUN
EXTERNAL CONDUCTIVE COATING
ALUMINIZED SCREEN

## DESCRIPTION AND RATING

The 24CP4-A is a magnetic-focus and deflection, direct-view all-glass picture tube which provides a 21\[^3/8\)- by 16\[^7/8\)-inch picture for television applications. The electron gun is designed for use with an external single-field ion-trap magnet. Other features of this tube include a high-quality gray faceplate which increases picture contrast and detail under high-ambient-light conditions, a reflective aluminized screen to increase light output, and a space-saving rectangular face shape. An external conductive coating serves as a filter capacitor when grounded.

## **GENERAL**

ELECTRICAL	
Heater Voltage	Volts
Heater Current	
Focusing Method—Magnetic	
Deflecting Method—Magnetic	
Deflection Angle, approximate	
Diagonal90	Degrees
Horizontal85	Degrees
Vertical	Degrees
Direct Interelectrode Capacitances, approximate	
Cathode to All Other Electrodes5	υυf
Grid-No. 1 to All Other Electrodes6	uuf
External Conductive Coating to Anode	
Maximum	υυf
Minimum	υυf
OPTICAL	
Phosphor Number—P4, Sulfide Type	
Fluorescent Color—White	
Phosphorescent Color—White	
Persistence—Short	
Faceplate—Gray	
Light Transmission at Center, approximate	Percent



MECHANICAL	
Over-all Length	Inches
Greatest Bulb Dimensions	
Diagonal	Inches
Width	Inches
Height	Inches
Minimum Useful Screen Dimensions	
Diagonal	Inches
Width	Inches
Height16⅓	Inches
Neck Length71/2	Inches
Bulb Number, ASA Designation—J192-A1	
Bulb Contact—Recessed Small-cavity Cap, JETEC No. J1-21	
Base—Small-shell Duodecal 5-Pin, JETEC No. B5-57	
Basing, JETEC Designation—12N	
Bulb Contact Alignment	
Anode Contact Aligns with Pin No. 6 Position ±30 Degrees	
Alloue Collider Alighs with the tot of osmon — 50 begrees	
Mounting Position—Any	
Net Weight, approximate	Pounds
MAXIMUM RATINGS	
DESIGN-CENTER VALUES*	
Anode Voltage†20,000 Max	Volts DC
Grid-No. 2 Voltage500 Max	Volts DC
Grid-No. 1 Voltage	
Negative-Bias Value	Volts DC
Positive-Bias Value	Volts DC
Positive-Peak Value	Volts
Peak Heater-Cathode Voltage‡	
Heater Negative with Respect to Cathode	
During Warm-up Period not to Exceed 15 Seconds	Volts
After Equipment Warm-up Period	Volts
Heater Positive with Respect to Cathode	
Tiedler Fositive with Respect to Cultique	VOIIS
TYPICAL OPERATING CONDITIONS	
Anode Voltage §	Volts DC
Grid-No. 2 Voltage	Volts DC
Grid-No. 1 Voltageπ	Volts DC
Focusing-Coil Current▲, approximate117	Milliamperes DC
Ion-Trap Field Intensity , approximate	Gausses
MAXIMUM CIRCUIT VALUES	
Grid-No. 1 Circuit Resistance1.5 Max	Megohms

<sup>\*</sup>The maximum ratings provide a ten-percent safety factor in accordance with the standard design-center system of rating cathode-ray tubes. The tube will withstand the combined effects of variations in line voltages and components provided the maximum design-center values are not exceeded by more than ten percent.

†Anode and grid-No. 3 which are connected together within the tube are referred to herein as anode.

If this tube is operated at voltages in excess of 16,000 volts, x-ray radiation shielding may be necessary to avert possible danger of personal injury from prolonged exposure at close range. The protective face-viewing window of apparatus using tubes of this type may provide such a safeguard. If the radiation measured in contact with this window does not exceed 6.25 milliroentgens per hour, the window will normally provide adequate protection.


‡Cathode should be returned to one side or to the midtap of the heater transformer winding.

§Brightness and focus quality decrease with decreasing anode voltage. In general, the anode voltage should not be less than 14,000 volts.

 $\pi$ For visual extinction of focused raster.


▲ For JETEC focusing coil No. 109 with distance from the yoke-reference-line to center-of-air-gap distance equal to 3¾ inches.

Single-field ion-trap magnet adjusted to optimum position, equivalent to 40 milliamperes through JETEC ion-trap magnet No. 117.



## NOTES:

- REFERENCE LINE IS DETERMINED BY THE PLANE OF THE UPPER EDGE OF THE SHOULDER OF THE REFERENCE-LINE GAGE (RETMA NO 116) WHEN THE GAGE IS RESTING ON THE CONF.
- 2. DEFLECTION ANGLE ON DIAGONAL IS 90 DEGREES.
- 3. ANODE TERMINAL ALIGNS WITH PIN-NO. 6 POSITION ± 30 DEGREES.
- 4. APPROXIMATE POSITION OF ION-TRAP MAGNET.
- 5. RECOMMENDED POSITION FOR CENTER OF FOCUSING FIELD.
- 6. EXTERNAL CONDUCTIVE COATING CONTACT AREA.



BASING DIAGRAM