



Two New Centrifuge Models

THE New International Size 1 Model SBV and Size 2 Model V Centrifuges embody the many time-proven features found in their predecessors — the Size 1 Type SB and Size 2 machines — and in addition incorporate important engineering improvements. A transformer-type speed controller replaces the resistance rheostat heretofore used and the Centrifuges are now shipped to you mounted on a permanently attached sub-base equipped with casters.

Speed Controller

Stepless, uniform speed control throughout the entire range is achieved and troublesome heating of — and heat radiation from — the controller is eliminated. Controller and two-hour automatic timer are mounted in an attractive enclosing cabinet conveniently located on the side of the Centrifuge steel guard.

Sub-Base Mounting

No assembly of any kind is necessary. No separate portable stand to bother with. Simply uncrate the completely assembled unit, wheel it to the electric outlet and plug

it in. Specially designed vibration dampeners, incorporated in the sub-base, provide maximum absorption of horizontal and vertical vibration and prevent their transmission to the floor of the laboratory.

Accessories

All interchangeable heads, shields, cups, and attachments listed for the discontinued SB and Size 2 machines fit the new models. Thus the Model SBV and Model 2V offer the same versatility and adaptability to your requirements. Send today for descriptive Bulletins V-1 and V-2 containing complete details.

INTERNATIONAL EQUIPMENT COMPANY

1284 SOLDIERS FIELD ROAD, BOSTON 35, MASS.