


Complete New Catalog describes  
the Latest Edition of  
**THE CARVER LABORATORY PRESS**




• Send for your copy of this new handy-size manual containing up-to-date information on the Carver Laboratory Press and its many uses.

**FRED S. CARVER INC.**  
**HYDRAULIC EQUIPMENT**

9 CHATHAM ROAD, SUMMIT, N. J.

**C&B**



**Reagent Chemicals**

C & B Reagent Chemicals are manufactured to meet definite standards of purity . . . standards which have been set up to insure products suitable for research and analytical use. These standards are based upon the publications of the Committee on Analytical Reagents of the American Chemical Society and our own experience of over thirty years in the manufacture of fine chemicals.

C & B Products are Distributed by  
Laboratory and Physician Supply Houses  
throughout the World.

Write for catalog, The COLEMAN & BELL Co., Inc.,  
Manufacturing Chemists, Norwood, O., U.S.A.

**COLEMAN & BELL**



**Light-Scattering** **INDICATING and RECORDING**  
**MICROPHOTOMETER**

FOR THE MEASUREMENT OF:

Droplet size of aerosols . . . Purity of proteins and other colloids . . . Rate of change of molecule size in solution . . . Particle size and concentration in dispersed systems . . . Concentration and size of undissolved particles . . . Opacity of almost-opaque materials . . . Molecular aggregation in antigen-antibody reactions . . . Microfluorescence in dilute solutions . . . Depolarization, turbidity, and dissymmetry of high-molecular-weight solutions . . . Light reflectance of dark surfaces . . . Minute precipitation, flocculation, and crystallization . . . Molecular weight of high polymers in solution . . . Scintillation efficiency of nuclear-radiation-sensitive crystals and phosphors . . . Microchemical turbidity analyses.

Excellent sensitivity.  
Completely a-c. operated.  
Has outlet for recorder operation.  
Internal electronic stabilization.

**FEATURES**

Compact . . . accessible.  
Fully accessible interior.  
Comparisons of light intensities indicated as decimal percentages.

Built-in stable d-c. amplifier.  
Maladjustment of the controls cannot damage the unit.  
Removable slit and optical systems.



Measures 20  
Micro-microlumens  
to 20 Lumens  
of  
Scattered Light



WRITE FOR BULLETIN 2182-K

**AMERICAN INSTRUMENT COMPANY, INC.**

SILVER SPRING, MARYLAND — IN METROPOLITAN WASHINGTON, D. C.